TS5322 Series Mini Spool Valve

Data Sheet





TS5322 Series Mini Spool Valve

Fluid dispensing not affected by fluid input pressure

The TS5322 Series Mini Spool Valve is based on a balanced spool design, to create a fast "ON/OFF" fluid dispensing function that is not affected by fluid input pressure. The spool action displaces a portion of the fluid back into the dispensing tip during shut off. This creates an automatic "suck-back" anti-drip feature.

An oil chamber is provided for use above the upper seal to create an additional liquid seal that will prevent moisture from being carried onto the spool. The design facilitates easy maintenance without the need for special tools.

The valve is designed to be opened by air pressure and closed by a return spring (single acting). A port is provided so that the valve may be connected for air closing without the spring (double acting).

The valve ships with:

Mounting bracket kit | Valve air hose | Luer lock fluid line | Fluid inlet fittings - 1/4" compression and Luer lock type | Dispensing tip selection pack | Oiler

TYPICAL APPLICATIONS

- Dispense beads of sealant to create form-inplace gaskets
- Dispensing small drops of oil into gear box
- Applying liquid flux, onto PCBA, during manufacturing process


KEY FEATURES & BENEFITS

- Dispense precise shots of medium to high viscosity fluids
- Automatic "suck-back"
- Oiler port for moisture sensitive fluids
- Compatible with UV fluids (TS5322D)

TS5322 Series Mini Spool Valve

Data Sheet





ACCESSORIES

- **Fluid reservoirs:** The valve can be fed from the TS1254 or TS1258 Pressure Tank, or from any size syringe barrel or cartridge.
- **Dispensing Tips:** Precision TT Series dispensing tips, from 14 27 gauge, are recommended for this valve type. For the complete dispensing tip offering please visit <u>www.techcon.com</u>

For Sales and Support: **Techcon Corporate Headquarters**

0800 Valley View Street, Cypress, California, 90630, USA. Gel: 1-714-230-2398 Gax: 1-714-828-2001 G-mail: eorders@okinternational.com Visit our website for more information and to contact the Techcon office nearest you. We have several offices worldwide that are ready to serve your needs.

techcon.com/contact-us

