

Training Program - 02. Tweezer categories (part 1)

Tweezer categories and materials



| | | HIGH PRECISION TWEEZERS | COATED/GRIP TWEEZERS | CUTTING TWEEZERS | PLASTIC TWEEZERS | CERAMIC TWEEZERS | ECONOMY TWEEZERS |
|-----|------|-------------------------|----------------------|------------------|------------------|------------------|------------------|
| | сх | | • | • | • | • | • |
| | SA | • | | • | • | • | |
| | s | | • | • | • | • | • |
| | С | • | | • | • | • | • |
| | NC | • | | • | • | • | • |
| | TA | | | • | • | • | • |
| | N | • | • | • | • | • | • |
| | BR | • | • | • | • | • | • |
| •00 | СР | • | • | • | • | • | • |
| •0• | CF | • | • | • | • | • | • |
| 131 | sv | • | • | • | • | • | • |
| 0 | DG | • | • | • | • | • | • |
| .0: | MZ _ | • | • | • | • | | • |
| *(1 | ZJ | • | • | • | • | | • |

Tweezer categories (Core Tweezers)

| | CATEGORY DESCRIPTION | MOST POPULAR STYLES | MATERIALS |
|--|--|---------------------|---|
| HIGH PRECISION TW | Handcrafted to have perfect tip symmetry and balance along with polished edges and superior no-scratch/antiglare satin finish. Typical applications include microscopy preparation, sample handling, precision manufacturing, electronic industry, watch making, general laboratory and medical applications. BIOLOGY TWEEZERS - Made of high-alloy stainless steel (DX) and superalloy (CX). The perfect choice to be used under microscope as their extra fine tips are ideal for handling extremely minute, delicate material and grids. | 0 3 5 2A 7 | CX - SA - S - C - NC - TA - N - BR - PB |
| HP - SUPER SLIM | Smooth scratch proof tips designed for handling sensitive parts and components. Applications include moving, gripping and manipulating flat parts, substrates and wafers. The smooth, flat tips enable gentle handling and minimum pressure on delicate parts. | 33A 35A 36A | SA - S - TA |
| | Long and slender tweezers especially suited for reaching in tight spaces or for working near heat sources. | SS 65A | SA - S - TA |
| COATED/GRIP TW ESD SAFE EPOXY COATING | Anti-Magnetic or Carbon precision tweezers with black ESD safe Epoxy coating (resistivity 10°-10° Ohm). The elastic Epoxy Coating provides enhanced operator comfort and impact resistance, in environments up to 120°C. Good resistance to many diluted acids and alkalis. | 0 4 | Handle Coating: NE Tweezers: SA - C |
| ESD SAFE DIAMOND COATING | Anti-Magnetic precision tweezers with ESD safe diamond coating (resistivity 10 ⁴ Ohm). This high hardness and high elasticity biocompatible coating protects tweezer tip from wear. These tweezers are ideally suited for handling of hard materials, demanding sample preparation, biological, clean room and high use applications. DC tip coating is available for any Techni-pro tweezer model. | 00 5 1 5A | Tip coating: DC Tweezers: SA - C - NC - TA |
| EGD GALE GITTI TIANDLE | Soft ESD safe ergonomic cushion grips (resistivity 10° Ohm) provide enhanced operator comfort and reduced finger stress when handling ESD sensitive components or small static items. | 2 5B | Handle grip: DN Tweezers: SA - C - NC |
| PTFE COATING | | 2A 7 | |
| | PTFE coating reduces the rate of heat during critical cryo work and reduces the corrosive action of acids and bases on tweezers tips. PTFE-coated tweezers are recommended when specimen material is fragile. | 2AB AA | Full body coating: T Tweezers: SA |
| | | •••••• | ••••••••••••••••••••••••••••••••••••••• |

Tweezer categories (Core Tweezers)

| | CATEGORY DESCRIPTION | MOST POPULAR STYLES | | | MATERIALS | |
|--|---|---------------------|-------|--------|---------------------------------------|--|
| CUTTING TW | Made from High Grade Carbon Steel for superior high precision cutting edges, these tweezers feature a tapered narrow design for narrow working spaces and are available with angled blades, predominantly angled blades, parallel blades, rounded tips, hard metal carbide blades and miniature size. Applications include cutting soft wires such as copper, gold, silver as well as magnetic wires and hard | | 14A | 15AGW | | |
| | | | 14AGW | 15AGHM | C-S | |
| | hairsprings. | | 152 | 15ARW | | |
| PLASTIC TW PLASTIC REPLACEABLE TIPS | Specially designed for the electronics industry, these tweezers feature durable and self-aligning replacement tips, anti-magnetic stainless steel handles and are available with a variety of tip geometries and materials: they offer a significant cost savings. Excellent for handling sensitive electronic components, and ceramic and glass parts where non-metallic non-scratching is critical. | | 2A | 242 | | |
| | | | 5 | 249 | Handle: SA Tips: CF - CP - SV - DG | |
| FULL PLASTIC | | | 7 | 259 | | |
| A STATE OF THE STA | Cost-effective alternative to metal tweezers for sensitive applications and handling scratch sensitive electronic parts, glass and ceramic substrates. Lightweight, | | 702A | 707 | CF - SV - DG - LC - LR | |
| | strong and sturdy material make them ideal for forensic, electronic and sample preparation applications. | | 705 | 709 | | |
| CERAMIC TW CERAMIC REPLACEABLE TIPS | Zirconia ceramic tips (MZ) and ESD safe ceramic tips (ZJ) are contamination free | | | | | |
| | as well as high temperature, wear and solder resistant. They feature alignable replaceable tips with stainless steel handles. High precision tips for high temperature | | 2A | 71 | Handle: SA Tips: MZ - ZJ | |
| | applications and handling of sensitive components, ceramic and glass parts where non-metallic non-scratching is critical. | | 7 | 72 | | |
| ECONOMY TW | | | 00 | 5 | | |
| | The most popular tweezers are also available in economical version at a very competitive price. Made in Asia and re-worked for a consistent performance. | | 2A | 7 | SA | |
| | personal personal management and to morror for a consistent personal management | | 3 | SS | | |
| | | | | | | |