

Tripp Lite 1111 W. 35th Street Chicago, IL 60609 USA Telephone: 773.869.1234 www.tripplite.com


Please see below under **Resources > Product Literature** for the Power Cord Selector Worksheet for both input and output power cord selection.

Isolator Series Dual-Voltage 115/230V 1800W 60601-1 Medical-Grade Isolation Transformer, C20 Inlet, 8 C13 Outlets

MODEL NUMBER: IS1800HGDV







Transformer with full CAN/ES/IEC/EN 60601-1 listing offers line isolation, step-up and step-down capabilities, and continuous noise filtering in protecting medical electronic equipment used in patient-care vicinities.

Description

The IS1800HGDV Isolator® Series Dual-Voltage 115/230V 1800W 50/60Hz Medical-Grade[™] Transformer with full CAN/ES/IEC/EN 60601-1 listing is ideal for protecting sensitive electronic equipment in patient-care vicinities. It can be configured for either step-up voltage, step-down voltage or pass-through voltage operation. Along with line isolation and continuous EMI/RFI line noise filtering, its surge protection rating of 240 joules suppresses excess voltage to prevent it from damaging connected equipment.

An internal low-impedance isolation transformer component offers 100% isolation from the input mains AC line. Faraday shield reduces the cumulative leakage current of the IS1800HGDV and connected equipment to levels less than 100 microamps, while removing utility switching transients and harmonics generated by other on-site loads and reducing the impact of utility-related surge conditions.

Transformer filtering provides continuous common-mode noise rejection with no wearable parts. The IS1800HGDV reduces 6000V IEEE 587 Category A and B ring wave and combination wave test surges to only 0.5V common mode.

Components connect to eight C13 outlets with fuse overload protection and a lighted on/off switch. The rugged all-metal unit housing ships ready for placement in any industrial, medical, office, network or audio/video environment. Requires a C19 AC input cord with country specific plug (sold separately).

Features

Full CAN/ES/IEC/EN 60601-1 Medical-Grade Listing with C20 Inlet and 8 C13 OutletsIdeal for protecting sensitive electronic equipment in patient-care vicinitiesReduces cumulative leakage current of Isolator and connected equipment to levels less than 100 µAInexpensive alternative to dedicated circuits and site electrical upgradesRugged all-metal housing designed to withstand frequent use in busy environmentsRequires a C19 AC input cord with country specific plug (sold separately).

Selectable 115/230V Input/Output Voltage Suitable for Most ApplicationsStep-up, step-down or pass-

Highlights

- Protects sensitive equipment from EMI/RFI line noise and surges
- Cumulative leakage current less than 100 µA
- Automatically shuts down all outlets in case of overload
- Offers complete isolation from input AC mains power
- Ideal for use in any industrial, network or medical environment

Package Includes

- IS1800HGDV Isolator Series Dual-Voltage 115/230V 1800W 60601-1 Medical-Grade Isolation Transformer
- (2) Fuse sets (115V and 230V operation)
- Input/output cable selector data sheet
- Owner's manual



through voltage operation (input frequency always equals output frequency)Internal low-impedance toroidal isolation transformer with Faraday shield offers 100% isolation from mains AC power lineAutomatically shuts down all outlets in case of overloadShips ready for placement in any industrial, medical, office, network or audio/video environment

Protects Connected Equipment from Dangerous Spikes, Surges and Line NoiseLine isolation, continuous noise filtering and 240 joules of AC surge protectionRemoves EMI/RFI noise, utility switching transients, load-generated harmonics and ground loopsFloating AC output prevents noise coupling from noisy ground circuitsReduces 6000V IEEE 587 Category A and B ring wave and combination wave test surges to only 0.5V common mode

Specifications

OVERVIEW	
UPC Code	037332200037
Efficiency	96%
Nominal Voltage / Frequency	115/230 VAC 50/60 HZ (Voltage Selected by Input Power Module Fuse Installation
VA / Watt Capacity	1800
Transformer Type	Medical Grade, Low Impedence Toroid- Line Isolation (Pass Through or Step UP or Step Down)
INPUT	
Nominal Input Voltage Description	115/230 VAC (Selected by Input Power Module Fuse Installation) Operating Input Voltage Range 100-125Vac or 200-250VAC
Input Frequency	50/60HZ
Maximum Surge Amps	100A
Input Current	15A @ 115V / 8A @ 230V
THDi	Less than 1%
Power Input Receptacle	IEC-320-C20
OUTPUT	
Output Voltage Regulation (Line Mode)	3.6%
Output (VA)	1800
Output (Watts)	1800
Output Receptacles	(8) C13
Output Nominal Voltage	115V/230V (Selected by Output Switch) Can also be step up or step down, Selected when Installing Fuses.
ISOLATION	
Output Isolation Transformer	Toroid with AC output Floating with Respect to Earth Ground
Leakage Current	Max AC Leakage Current 80 (uA)
SURGE / NOISE SUPPRESSION	



Tripp Lite 1111 W. 35th Street Chicago, IL 60609 USA Telephone: 773.869.1234 www.tripplite.com

240	
Reduced to 0.5v Common Mode	
35-65db	
Metal (Cabinet)	
White	
Convection	
27.99 x 44.50 x 50.01	
11.02 x 17.52 x 19.69	
23.23	
51.21	
5.51 x 11.81 x 13.78	
14 x 30 x 35	
51.21	
23.23	
0 C-40 C(32F to 104F), Intended Application is in a controlled environment at approx. 25 C.	
-15 C to 50 C (5F to 122F)	
0-3000M (0-10,000 Ft)	
5% to 95% RH (Non-Condensing)	
2X15A @ 115V and 2X8A at 230V (Both Fuses included with Product as Accesories)	
Input Voltage equals Output Voltage OR 120V input equals 230V output OR 230V Input equals 120V output - (Selectable when installing Fuses) Input Frequency always equals Output Frequency	
IEC 60601-1; CAN/CSA-C22.2 No. 60601-1 (Canada); NOM (Mexico)	
RoHS; CE (Europe)	
WARRANTY	
2-year limited warranty	

© 2022 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does



not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <u>https://www.tripplite.com/products/product-certification-agencies</u>